


Lakeland Disposable and Chemical Selection Flowchart



* For details on Type 4 and Type 3 solutions, contact your Lakeland Sales Representative or call Customer Service at 800-645-9291.

** Must be worn over thermally protective clothing, such as fire resistant cottons, aramids or modacrylics.

*** Refer to permeation data on next page for which ChemMax[®] is indicated for a given hazard.

This is a general guide to selecting garments only, and should not be used as the definitive or only tool in garment selection. It is the responsibility of the user to select garments or products which are appropriate for each intended use and which meet all specified government and industry standards.

Lakeland Disposable and Chemical Clothing Performance and Selection **Quick Reference Guide** . Theat sealed seam

Eakeland

La	keland	10	ie Card cat	2 cord with	comot pic	ohat hs	Jon Pus 21	Jon Artill	olon CHERT	inna isen	ed Search Bou	nd seam	as Sealed	in Ind Searn The Che	atseated seat	n mhot a
	Dirt, Oil and Grease	•	•	•	*	•	•	•	•	•		•				
General	Hazardous Dry Particulates		•	•	*	•	•	•	•	•		•			ļ	
Protection	Non-hazardous Liquids	•	•	•	☆		•	•	•	•		•				
	Welding, Cutting and Grinding					*	•	•								
	Non-hazardous Liquids (Aerosol)		•	•	*		•	•	•	•		•				
Aerosol Spray	Paint and Hazardous Liquids – Spray		•	•	*	•	•	•	•	•	•	•	•	•	•	
	Dry Particle - Aerosols		•	•	☆	•	•	•	•	•	•	•	•			
Chemical	Low Exposure, Low Risk Chemical Splash			•	•			•	•	•	•	*	•			
Splash	High Exposure / High Risk							•			•		•	•	<u>☆</u>	•
	Hazmat, NFPA Certified															☆
Hazmat	Hazmat, Maritime													★	•	•
	Hazmat, Non-Certified							•			•		•	•	_ ☆	•
	Flammable Environments (Aerosol)					*	•	•								
Flame Resistance	Flammable Liquids							*								
	Chemical Flash Fire					•	•	•								•
Critical Environment / Biohazard	Clean Rooms			•	*											
	Paint Booth			•	☆			•	•							
	Bloodborne Pathogens [4]			•	•			•	•	•	☆	•	•	•	•	•
	Waste Water Treatment			•	•			•	•	☆	•	•	•	•	•	
[2]	Comfort	5	4	2	2	4	4									
	Barrier	1	2	5	5	2	2									
	Durability	1	4	4	3	3	4									

Chart Key

- [1] Pyrolon[®] family of products must be worn over thermally protective garments, such as FR Cotton or FR meta aramids
- [2] Interceptor[®] is available certified for NFPA 1991 and CE Type 1
- [3] Relative Ratings: 1 is lowest, 5 highest, based on EN/ISO test results and relative difference between fabrics
- [4] Lakeland recommends sealed seams for protection against infectious diseases
- = May meet requirements depending on degree of hazard
- \mathbf{X} = Best seller for application

Available Seams



Economical stitching method for general applications


Generally not used for chemical protective clothing and commonly found on disposable clothing

Sewn and **Bound Seam** Joins two pieces of material with an overlay of similar material

Chain stitched through all of the layers for a clean finished edge Provides increased holdout of liquids

and dry particulates





with a heat activated tape Provides liquid proof seams, and is

especially useful for Level A and B chemical protective clothing.

ZoneGard[®]

- 38 gram heavy Spunbonded Polypropylene
- Entry level garment for dirty work

SafeGard® SMS

- 45 gram Spunbonded Meltblown Spunbonded Polypropylene
- High breathability
- Good barrier to dry particulates, aerosols and light liquid hazards

MicroMax® NS

- Microporous Film laminated to Polypropylene substrate
- Excellent barrier to dry particulates and liquid hazards
- Blood-borne pathogen/viral barrier tested
- Top seller in the industrial market category; refer to Additional Reference Material [1] [2] [4]

MicroMax[®]

 Same protection as MicroMax[®] NS with the addition of a rip-stop scrim for added durability.

MicroMax[®] Cool Suit:

- Breathable SMS back panel
- Best combination for comfort and barrier

Pyrolon[®] Plus 2

- Flame Resistant
- Dry and light liquid splash protection
- Meets NFPA 2113 requirements
- See comparison data against Chinese FR Spunlaced and FR SMS products [3] [5] [6] [7]

Pyrolon[®] XT

 Same as Pyrolon Plus 2 with rip-stop scrim for added durability

Pyrolon[®] CRFR

- Chemical Resistant and Flame Resistant
- Excellent for protection against flammable liquids
- Specifically designed for petrochemical, refinery and utility applications
- Meets NFPA 2113 requirements

• For further information refer to [2]

ChemMax® 1

- Polyethylene coated Polypropylene fabric
- Good hold out to acids and bases
- Economical and lightweight

ChemMax[®] 2

- Dow Saranex[®] 23P film laminated to bi-component spunbond nonwoven
- Moderate to high chemical resistance
- · Very good choice for chemical handling and environmental clean-up

ChemMax[®] 3

- Softer feel
- Excellent choice for Petrochemical and Hazmat operations
- Chemical Warfare Agent tested

ChemMax[®] 4

- 6 layer protective barrier film protection
- Superior chemical resistance
- Soft flexible feel not found in competitive fabrics
- Excellent choice for Hazmat and Petrochemical operations

Interceptor[®]

- Lakeland's highest level of chemical protection
- NFPA 1991 and CE type 1 certified
- Level A configurations for gas/vapor hazards
- Also available in non-level A configurations

Additional Reference Material Available

at www.lakeland.com/resources.html

Literature

[1] Disposable and Chemical Protective Clothing Performance and Selection Guide

[2] Disposable and Chemical Protective Clothing **Buyers** Guide

[3] Pyrolon[®] Plus 2 vs Alternate FR Disposables Guide

Videos

[4] Disposable Clothing Case Study [5] Pyrolon[®] Plus 2 Disposable FR Garments [6] Pyrolon[®] Plus 2 vs FR Alternatives [7] Pyrolon[®] Plus 2 Repellency

Comparative Chemical Fabric Performance	e Data
---	--------

Basis WeightASTM D3776- 90 & 07512.29 oz/y24.3 oz/y24.5 oz/y26.5 oz/y29.0 oz/y2ThicknessD1777-7515 mil16 mil16 mil24 mil25 milTrapezoidal Tear MD Trapezoidal Tear XDASTM D573314 lbf30 lbf26 lbf52 lbf44 lbfTrapezoidal Tear XDASTM D573314 lbf30 lbf20 lbf37 lbf58 lbfASTM F1001 Permeation Times: Green denotes >480 minutesAcetonitrileAcetonitrileAnhydrous Ammonia1,3 ButadieneCarbon DisulfideDichloromethaneDichloromethaneDiethylamineDimethyl FormamideEthyl AcetateEthylene OxideMethyl ChlorideMethyl ChlorideMethyl ChlorideTerraceSodium HydroxideSulfuric AcidTerraceSulfuric AcidTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerraceTerrace							
Basis Weight90 & D7512.29 OZ/Y24.3 OZ/Y24.3 OZ/Y26.5 OZ/Y29.0 OZ/Y2ThicknessD1777-7515 mil16 mil16 mil24 mil25 milTrapezoidal Tear MD Trapezoidal Tear XDASTM D573314 lbf30 lbf26 lbf52 lbf44 lbfTrapezoidal Tear XDASTM D573314 lbf13 lbf20 lbf37 lbf58 lbfASTM F1001 Permeation Times: Green denotes >480 minutesAcetoneAcetonitrileAnhydrous Ammonia </th <th></th> <th>Test Method</th> <th>ChemMax®1</th> <th>ChemMax®2</th> <th>ChemMax®3</th> <th>ChemMax®4</th> <th>Interceptor[®]</th>		Test Method	ChemMax®1	ChemMax®2	ChemMax®3	ChemMax®4	Interceptor [®]
Trapezoidal Tear MD ASTM D5733 14 lbf 30 lbf 26 lbf 52 lbf 44 lbf Trapezoidal Tear XD ASTM D5733 14 lbf 13 lbf 20 lbf 37 lbf 58 lbf ASTM F1001 Permeation Times: Green denotes >480 minutes	Basis Weight		2.29 oz/y ²	4.3 oz/y ²	4.5 oz/y ²	6.5 oz/y ²	9.0 oz/y ²
Astm D5733Astm D573314 lbf13 lbf20 lbf37 lbf58 lbfASTM F1001 Permeation Times: Green denotes >480 minutesAcetoneAcetonitrileAcetonitrileAcetonitrileAnhydrous Ammonia1,3 ButadieneCarbon DisulfideChlorineDichloromethaneDichloromethaneDiethylamineDiethylamineDimethyl FormamideEthyl AcetateEthyl AcetateMethanolMethanolMethanolMethanolSodium HydroxideSulfuric AcidTetrachloroethyleneIntraceneeSulfuric AcidTetrachloroethyleneIntraceneeSodium HydroxideSulfuric AcidIntraceneeInternationIntracenee <t< th=""><th>Thickness</th><th>D1777-75</th><th>15 mil</th><th>16 mil</th><th>16 mil</th><th>24 mil</th><th>25 mil</th></t<>	Thickness	D1777-75	15 mil	16 mil	16 mil	24 mil	25 mil
Trapezoidal Tear XD14 lof13 lof20 lof37 lof58 lofASTM F1001 Permeation Times: Green denotes >480 minutesAcetoneAcetonitrileAcetonitrileAnhydrous Ammonia1,3 Butadiene1,3 Butadiene1,3 ButadieneCarbon DisulfideChlorineDichloromethaneDichloromethaneDiethylamineDiethylamineDimethyl FormamideEthyl AcetateEthyl AcetateEthyl AcetateIthyl AcetateIthyl AcetateIthyl ChlorideIthyl C	Trapezoidal Tear MD		14 lbf	30 lbf	26 lbf	52 lbf	44 lbf
AcetoneImage: set of the set o	Trapezoidal Tear XD		14 lbf	13 lbf	20 lbf	37 lbf	58 lbf
ActernitrileImage: constraint of the second sec	ASTM F1001 Permeation	Times: Green	denotes >480) minutes			
Anhydrous AmmoniaImage: state integral and st	Acetone						
1,3 Butadiene Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Chlorine Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Dichloromethane Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Dichloromethane Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Diethylamine Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Dimethyl Formamide Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Ethylance Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Hydrogen Chloride Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Methanol Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Nitrobenzene Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Sodium Hydroxide Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Sulfuric Acid Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Sulfuric Acid Image: Carbon Disulfide Image: Carbon Disulfide Image: Carbon Disulfide Sulfuric Acid Image: Carbon	Acetonitrile						
Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideChlorineImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideDichloromethaneImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideDimethyl FormamideImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideDimethyl FormamideImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideEthyl AcetateImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideHydrogen ChlorideImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideMethanolImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideNitrobenzeneImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideSodium HydroxideImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideSulfuric AcidImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideTetrachloroethyleneImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon DisulfideTetrahydrofuranImage: Carbon DisulfideImage: Carbon DisulfideImage: Carbon Disulfide	Anhydrous Ammonia						
ChlorineImage: state in the stat	1,3 Butadiene						
DichloromethaneImage: Constraint of the symbolImage: Constraint of the symbolDiethylamineImage: Constraint of the symbolImage: Constraint of the symbolDimethyl FormamideImage: Constraint of the symbolImage: Constraint of the symbolDimethyl AcetateImage: Constraint of the symbolImage: Constraint of the symbolEthylane OxideImage: Constraint of the symbolImage: Constraint of the symboln-HexaneImage: Constraint of the symbolImage: Constraint of the symbo	Carbon Disulfide						
Diethylamine Imathyl Formamide </th <th>Chlorine</th> <th></th> <th></th> <th></th> <th></th> <th></th> <th></th>	Chlorine						
Dimethyl Formamide Image: Sector of the se	Dichloromethane						
Ethyl Acetate Image: Constraint of the system of the s	Diethylamine						
Ethylene Oxide Image: Children of the system of the syst	Dimethyl Formamide						
n-Hexane Image: Chloride Image: Chloride Hydrogen Chloride Image: Chloride Image: Chloride Methanol Image: Chloride Image: Chloride Methyl Chloride Image: Chloride Image: Chloride Nitrobenzene Image: Chloride Image: Chloride Sodium Hydroxide Image: Chloride Image: Chloride Sulfuric Acid Image: Chloride Image: Chloride Tetrachloroethylene Image: Chloride Image: Chloride Tetrahydrofuran Image: Chloride Image: Chloride	Ethyl Acetate						
Hydrogen Chloride Image: Sector of the sec	Ethylene Oxide						
Methanol Image: Constraint of the system Methyl Chloride Image: Constraint of the system Methyl Chloride Image: Constraint of the system Nitrobenzene Image: Constraint of the system Sodium Hydroxide Image: Constraint of the system Sodium Hydroxide Image: Constraint of the system Sulfuric Acid Image: Constraint of the system Tetrachloroethylene Image: Constraint of the system Tetrahydrofuran Image: Constraint of the system	n-Hexane						
Methyl Chloride Image: Constraint of the second s	Hydrogen Chloride						
Nitrobenzene Image: Constraint of the second seco	Methanol						
Sodium Hydroxide Solitaria Sulfuric Acid Sulfuric Acid Tetrachloroethylene Sulfuric Acid Tetrahydrofuran Sulfuric Acid	Methyl Chloride						
Sulfuric Acid Image: Sulfuric Acid Tetrachloroethylene Image: Sulfuric Acid Tetrachloroethylene Image: Sulfuric Acid Tetrachloroethylene Image: Sulfuric Acid	Nitrobenzene						
Tetrachloroethylene Tetrahydrofuran	Sodium Hydroxide						
Tetrahydrofuran and a second an	Sulfuric Acid						
	Tetrachloroethylene						
	Tetrahydrofuran						
Toluene	Toluene						

Pyrolon[®] CRFR Penetration Data, 2.5 Mil, ASTM F903

Challenge Chemical	CAS Number	Physical State	Penetration Result
Acetone	67-64-1	Liquid	>60
Benzene	71-43-2	Liquid	>60
Diesel Fuel	N/A	Liquid	>60
Crude Oil	N/A	Liquid	>60
Hydrochloric Acid	7647-01-0	Liquid	>60
Sodium Hydroxide, 50%	1310-73-2	Liquid	>60

Note: A complete listing of all chemicals that have been tested, and their performance data, can be found at: www.lakeland.com/chemmax-chemical-search.html

ATTENTION!

As always, decisions regarding choice and usage of chemical protective clothing for a particular situation must be made by trained and gualified safety professionals in accordance with OSHA and EPA rules and regulations. Please see Warranty and Warnings on pages 20-21 of the Lakeland Disposable and Chemical Protective Clothing Buyers Guide for complete details.



ChemMax[®] 2



Coverall C44412 Bound Seam Zipper with storm flap Sizes: S - 5XL Case Pack: 12



Coverall C72110 Sealed Seam Collar

- Storm flap over zipper. Elastic wrists Elastic ankles
- Sizes: S 5XL Case Pack: 6



Coverall

C44414 Bound Seam Zipper with storm flap

Attached hood

Attached boots

Elastic wrists

Sizes: S – 5XL

Case Pack: 12

Coverall C72130 Sealed Seam Elastic face Elastic wrists Elastic ankles Sizes: S – 5XL Case Pack: 6



Zipper with storm flap



Coverall

Elastic wrists

Elastic ankles

Sizes: S – 5XL

Case Pack: 12

C44417 Bound Seam

• Zipper with storm flap

Elastic wrists




- Attached hood
- Attached boots

- Sizes: S 5XL Case Pack: 6
- Case Pack: 6


ChemMax[®] 2 offers quality, value, durability and the proven protection of Dow Saranex® 23P barrier film

ChemMax[®] 2 is the second level of barrier protection in the new ChemMax® line of products from Lakeland Industries. ChemMax® 2 is a superior and economical chemical protective suit developed using the knowledge and expertise that you have come to expect from Lakeland. The unparalleled strength and softness of ChemMax® 2 features Dow Saranex[®] 23P film on two layers of a unique bi-component spunbond nonwoven substrate and provides protection for chemical mixing and handling, environmental clean up, hazardous materials remediation and response, pharmaceutical manufacturing, spray painting and general industry. ChemMax® 2 is useful in protecting against hazardous chemicals and contaminants found in the work place.



Coverall C44428 Bound Seam

- Zipper with storm flap
- Attached hood Elastic wrists
- Elastic ankles Sizes: S – 5XL
- Case Pack: 12



Coverall C72165 Sealed Seam

- Respirator fit hood
- Storm flap over zipper Attached boots with
- boot flaps
 - Velcro[®] closure over zipper



ChemMax[®] 2 Physical Properties

Bound Seams

Light Liquid

Protection

Property	Test Method	Units	ChemMax® 2	
Basis Weight	ASTM D3776	oz/sy	4.3	
Grab Tensile MD		ASTM D5034 pounds		
Grab Tensile XD	ASTM D5034	pounds	33.9	
Trapezoidal Tear MD	ASTM D5733	pounds	29.95	
Trapezoidal Tear XD	ASTM D5/33	pounds	12.47	
Ball Burst	ASTM D751	pounds	48	
Surface Resistance	EN1149-1:2006	Pass/Fail	Pass	

Permeation Data for ASTM Recommended List of Chemicals for Evaluating Protective Clothing Materials (ASTM F1001)

Challenge Chemical	CAS Number	Physical State	ChemMax® 2
Acetone	67-64-1	Liquid	9
Acetonitrile	75-05-8	Liquid	<15
Ammonia Gas	7664-41-7	Gas	15
1,3-Butadiene Gas	106-99-0	Gas	>480
Carbon Disulfide	75-15-0	Liquid	imm.
Chlorine Gas	7782-50-5	Gas	>480
Dichloromethane	75-09-2	Liquid	imm.
Diethylamine	109-89-7	Liquid	imm.
Dimethyl Formamide	68-12-2	Gas	18
Ethyl Acetate	141-78-6	Liquid	21
Ethylene Oxide Gas	75-21-8	Gas	24
n-Hexane	110-54-3	Liquid	21
Hydrogen Chloride Gas	7647-01-0	Gas	>410
Methanol	67-56-1	Liquid	>480
Methyl Chloride Gas	74-87-3	Gas	>480.
Nitrobenzene	98-95-3	Liquid	45
Sodium Hydroxide, 50%	1310-73-2	Liquid	>480
Sulfuric Acid, 98%	7664-93-9	Liquid	>480
Tetrachloroethylene	127-18-4	Liquid	imm.
Tetrahydrofuran	109-99-9	Liquid	imm.
Toluene	108-88-3	Liquid	imm.

ND = None Detected

> = greater than

L = liquid

G = gasNumbers reported are averages of samples tested by the ASTM F739 test method. Sample results do vary and therefore averages for these results are reported.

Warnings:

1. ChemMax[®] 2 is not flame resistant and should not be used around heat, flame sparks, or in potentially flammable or explosive environments. 2. Garments made of ChemMax® 2 should have slip resistant or anti-slip materials on the outer surface of boots, shoe covers or other garment surfaces in conditions where slipping could occur.

Note: Chemical Resistance Data is in accordance with ASTM F-739 test method. Testina is performed on fabric samples only, not finished aarments. Sources for all test data are independent laboratory conditions and not actual use conditions.


800-645-9291 • www.lakeland.com • info@lakeland.com



Liquid Splash/ **Chemical Barrier**

Disposable and Chemical Clothing Sizing Charts

This following chart is a guide for garment selection. Proper fit varies with individual body shape and under clothing. Test garment for proper fit before use, as garment performance depends on selecting appropriate size. If you have any questions regarding your size call Lakeland Customer Service Toll Free at 800-645-9291.



ANSI/ISEA 101-2014 Recommended Sizing Chart for Limited Use Disposable Coveralls

Weight in Pounds (Kilograms)

